

**Nameplate Specifications**

Phase	1	Output HP	10 Hp
Output KW	7.5 kW	Voltage	208 V
Speed	3500 rpm	Service Factor	1
Frame	215T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	83.8 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	46.0 A	Power Factor	93.2
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	G
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	037646-1115	Connection Drawing	A-EE9048MF

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023