

Nameplate Specifications

Output HP	1/10 Hp	Output KW	0.07 kW
Frequency	50 Hz	Voltage	230 V
Current	0.7 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	42Y	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Resilient Rings	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	10.50 in	Frame Length	3.67 in
Shaft Diameter	0.500 in	Shaft Extension	5.8 in
Outline Drawing	DE3F7114-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2022