

Nameplate Specifications

Phase	3	Output HP	10 & 2.50 Hp
Output KW	7.5 & 1.9 kW	Voltage	460 & 460 V
Speed	1765 & 875 rpm	Service Factor	1.15 & 1.15
Frame	215T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	86.5 & 81.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	12.5 & 4.3 A	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	1VT	KVA Code	K
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4/8	Rotation	Reversible
Resistance Main	1.665 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.375 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	SS620684	Connection Drawing	EE7322