

### Nameplate Specifications

Output HP	1/2 Hp	Output KW	0.37 kW
Frequency	60 Hz	Voltage	200-230/460 V
Current	4.60/ 2.30 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

### Technical Specifications

Electrical Type	Permanent Split Capacitor	Poles	6
Rotation	Reversible	Mounting	Lug
Motor Orientation	Vertical Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	9.56 in
Frame Length	5.82 in	Shaft Diameter	0.500 in
Shaft Extension	3.00 in		
Outline Drawing	5KCP39SGU073S	Connection Drawing	NP24X350050

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2022