

PRODUCT INFORMATION PACKET

Model No: 215TTDW7377

Catalog No: Y202

Other Purpose Motor, 5 HP, 3 Ph, 60 Hz, 230/460/796 V, 1200 RPM, 215T Frame, DP



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230/460/796 V
Current	16.6/8.3/4.8 A	Speed	1130 rpm
Service Factor	1.15	Phase	3
Efficiency	84 %	Power Factor	68
Duty	Oil Well	Insulation Class	F
Design Code	D	KVA Code	H
Frame	215T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	N
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	2.48 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	17.30 in
Frame Length	11.15 in	Shaft Diameter	1.375 in
Shaft Extension	3.47 in	Assembly/Box Mounting	F2/F1 Capable
Connection Drawing	A-EE7326C	Outline Drawing	A-SS86500-1115



