

Nameplate Specifications

Phase	3	Output HP	5 & 2.22 Hp
Output KW	3.7 & 1.7 kW	Voltage	200-230 & 200-230 V
Speed	1775 & 1175 rpm	Service Factor	1.15 & 1.15
Frame	215T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	85.5 & 81.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	8.65-8.2 & 7.8-7.4 A	Power Factor	78.9
Duty	Continuous	Insulation Class	F
Design Code	2VT	KVA Code	N
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//6	Rotation	Fixed Clockwise
Resistance Main	.785 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	17.30 in
Frame Length	11.15 in	Shaft Diameter	1.375 in
Shaft Extension	3.47 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7317	Outline Drawing	A-SS86500-1115