

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|------------|
| Output HP | 5 Hp | Output KW | 3.7 kW |
| Frequency | 60 Hz | Voltage | 200 V |
| Current | 15.9 A | Speed | 1170 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Efficiency | 89.5 % | Power Factor | 76 |
| Duty | Continuous | Insulation Class | B |
| Design Code | B | KVA Code | H |
| Frame | 215T | Enclosure | Drip Proof |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6307 | Opp Drive End Bearing Size | 6206 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 12 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Across The Line |
| Poles | 6 | Rotation | Reversible |
| Resistance Main | 1.898 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | T | Overall Length | 18.55 in |
| Frame Length | 12.40 in | Shaft Diameter | 1.375 in |
| Shaft Extension | 3.47 in | Assembly/Box Mounting | F1 ONLY |
| Outline Drawing | SS86500-1240 | Connection Drawing | 005102.01 |