

### Nameplate Specifications

Output Watts	16 W	Frequency	60 Hz
Voltage	115 V	Current	0.4 A
Speed	1550 rpm	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	UNIT BEARING	Enclosure	Totally Enclosed Air Over
Thermal Protection	Electronic	Ambient Temperature	55 °C
UL	Yes	CSA	Y
CE	N		

### Technical Specifications

Electrical Type	Electronically Commutated Motor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Opposite Shaft End
Mounting	2 BOSS/OSE 5 HOLES	Motor Orientation	Any
Frame Material	Aluminum	Shaft Type	1/4-20 THREAD
Overall Length	3.85 in	Frame Length	3.52 in
Shaft Diameter	0.250 in	Shaft Extension	0.33 in
Outline Drawing	26665-Erwin		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022