

Nameplate Specifications

| | | | |
|------------------------|--------------------------|----------------------------|-----------------------------|
| Phase | 3 | Output HP | 10 & 7.50 Hp |
| Output KW | 7.5 & 5.6 kW | Voltage | 208-230/460 & 190/380 V |
| Speed | 3525 & 2930 rpm | Service Factor | 1.15 & 1.15 |
| Frame | 215TC | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Efficiency | 90.2 & 89.5 % |
| Ambient Temperature | 40 °C | Frequency | 60 & 50 Hz |
| Current | 25.9-23.6/11.8 & 22/11 A | Power Factor | 87.9 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | H |
| Drive End Bearing Size | 6309 | Opp Drive End Bearing Size | 6206 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 43 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Across The Line |
| Poles | 2 | Rotation | Reversible |
| Resistance Main | .8 Ohms | Mounting | Bolt-on Base |
| Motor Orientation | Horizontal Or Shaft Down | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | T | Overall Length | 19.47 in |
| Frame Length | 11.15 in | Shaft Diameter | 1.375 in |
| Shaft Extension | 3.12 in | Assembly/Box Mounting | F1/F2 CAPABLE |
| Connection Drawing | 005010.01 | Outline Drawing | SS88652-1115 |