

Nameplate Specifications

Phase	3	Output HP	6 Hp
Output KW	4.5 kW	Voltage	460 V
Speed	1160 rpm	Service Factor	1
Frame	254T	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Efficiency	84 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	9.5 A	Power Factor	69
Duty	60 Minute	Insulation Class	H
Design Code	A	KVA Code	J
Drive End Bearing Size	309	Opp Drive End Bearing Size	309
UL	No	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	6	Rotation	Reversible
Resistance Main	1.81 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 1000:1		
Outline Drawing	B-SS203673-1175	Connection Drawing	A-EE7300T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024