

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 254TTDX4017

Catalog No: U213

Close-Coupled Pump Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 3600 & 3000 RPM,
254JP Frame, DP



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord


Nameplate Specifications

Phase	3	Output HP	20 & 15 Hp
Output KW	14.9 & 11.2 kW	Voltage	230/460 & 190/380 V
Speed	3520 & 2925 rpm	Service Factor	1.15 & 1.15
Frame	254JP	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	91 & 90.2 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	46/23.1 & 42/21 A	Power Factor	88.6
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	F
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications


Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.485 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JP	Overall Length	25.29 in
Frame Length	13.40 in	Shaft Diameter	1.250 in
Shaft Extension	8.15 in	Assembly/Box Mounting	F1/F2 Capable
Connection Drawing	A-EE7308K	Outline Drawing	A-SS86519-1340

SS86519



DASH	FR.	C	BS	AG	MOUNTING
1545	256JP	27.34	9.43	19.22	F1 OR F2
1340	254JP	25.29	7.68	17.17	F1 OR F2
1515	254/256JP	27.04	9.43	18.92	F1 OR F2

- NOTES:
1. NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.
 2. BOX CAN BE MOUNTED IN 90° STEPS.
 3. BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°. (EXCEPT AS NOTED.)

7	ADDED 1545 PER NMR-0186853	SD 11/26/2019	AB	TOLERANCES UNLESS SPECIFIED		DRAWN DJK 10-19-1993			
6	UPDATED DRAWING	TJW 04/27/2007		DEC. INCHES		CHK ML 10-22-1993			
5	REDRAWN IN AUTOCAD	TAT 07-13-2004	ML	.X ±.1		APPD DRN 10-22-1993			
4	ADD'D TOLERANCE TO THIRD STEP OF SHAFT CN 28604	NJS 02-28-2000		.XX ±.03		SCALE 3=16			
3	UPDATED CONDUIT BOX CN 28427	TJB 01-31-2000		.XXX ±.005	TITLE OUTLINE 250JP FR.-BB-TS-DR.PR.-'C' FACE				REF
2	-1515 WAS FOR 256JP FR. ONLY CN 18683	KL 10-11-1994		.XXXX ±.0005	MAT'L.				FMF
NO.	REVISION	BY & DATE	CHK	ANG ±7'30"	FINISH				PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP		CAD FILE ss86519		SIZE A	DRAWING NO. SS86519	PAGE OF
			DIST LB						REV. 7

LOW VOLTAGEHIGH VOLTAGE

VIEW OF TERMINAL END

			TOLERANCES UNLESS SPECIFIED			 REGAL - BELOIT CORPORATION	DRAWN PGK 06-04-1997		
NO.	REVISION	BY & DATE	CHK	ANG	± 7'30"		CHK	ML	06-05-1997
E	CORRECTED IEC MARKINGS ECD-0111208	WGJ 01-23-2017	EMH	DEC.	INCHES	TITLE CONNECTION DIAGRAM DELTA CON. - 3Ø - 9 LEADS	APPD	GK	06-15-1997
D	RE-DRAWN WITH REGAL LOGO ECD-0110493	WGJ 09-30-2016	EMH	.X	± .1				
8	ADDED IEC DESIGNATIONS MU95020	TJW 4/30/2010	MJS	.XX	± .02				
7	REVISED HIGH VOLTAGE L2 WAS L3 CN52600-354	MRB 09-21-1998		.XXX	± .005				
6	REDRAWN ON CADD	PGK 06-05-1997		.XXXX	± .0005				
						MAT'L.			
						FINISH			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT						RFP	CAD FILE EE7308K		SIZE
						DIST			A
							DRAWING NO. PAGE OF		REV.
							EE7308K		E

CERTIFICATION DATA SHEET

Model#: 254TTDX4017 BC
 CONN. DIAGRAM: A-EE7308K
 OUTLINE: A-SS86519-1340

WINDING#: K2152191 NONE 1
 ASSEMBLY: F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
20&15	14.9&11.2	3600	3520&2925	254JP	DP	F	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	230/460#190/ 380	46/23.1&42/21	ACROSS THE LINE	CONTINUOU S	F4	1.15/1.15	40	3300

FULL LOAD EFF: 91&90.2	3/4 LOAD EFF: 91.7	1/2 LOAD EFF: 90.2	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 88.6&88	3/4 LOAD PF: 85.5	1/2 LOAD PF: 78	89.5	SQ CAGE IND RUN	14 / 7

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
30 LB-FT	288 / 144	52.5 LB-FT 175	86.5 LB-FT 288	45

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
78 dBA	88 dBA	0.65 LB-FT^2	18 LB-FT^2	15 SEC.	2	160 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL	BALL	POLYREX EM	JP	NONE	NONE	AISI 1045 (C-240)	ROLLED STEEL
6309	6208						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

*
N
O
T
E
S
*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE
ENCODER: NONE
NONE NONE
NONE NONE PPR
BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
- FT-LB NONE V NONE Hz

DATE: 06/23/2017 03:38:56 AM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.

Data Sheet

Date: 6/29/2017

Customer: _____

Attention: _____

Submitted by: FAREEDA DUDEKULA



254TTDX4017

Submittal

Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	7.0	9.0	13.5	18.0	23.1	26.5	29.5	144	
Torque (ft-lb)	0.00	7.5	15.0	22.2	30.0	34.5	37.5	52.5	
RPM	3600	3580	3565	3545	3520	3,515	3490	0	
Efficiency (%)		87.0	90.2	91.7	91.0	91.0	90.2		
P.F. (%)	9.0	60.0	78.0	85.5	88.6	89.0	89.0	40.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle					
Speed (RPM)	0	1800	3050	3520	3600					
Current (Amps)	144	130	90.0	23.1	7.0					
Torque (ft-lb)	52.5	48.0	86.5	30.0	0.00					
<div><div>— Efficiency (%) — P.F. (%) — Current (Amps)</div><div>EFFICIENCY, P.F., AND CURRENT VS. LOAD</div></div>						Information Block				
						HP		20.0		
						Sync. RPM		3600		
						Frame		254		
						Enclosure		DP		
						Construction		TDX		
						Voltage		230/460#190/381V		
						Frequency		60 Hz		
						Design		A		
						LR Code letter		F		
						Service Factor		1.15		
						Temp Rise @ FL		45 ° C		
						Duty		CONT		
						Ambient		40 ° C		
						Elevation		1,000 feet		
						Rotor/Shaft wk²		0.65 Lb-Ft²		
						Ref Wdg		K2152191 NONE		
Sound Pressure @ 1M		78 dBA								
VFD Rating		NONE								
Outline Dwg		A-SS86519-1340								
Conn. Diag		A-EE7308K								
Additional Specifications:										
0										
0										
EQUIV CKT (OHMS / PHASE)										
R1		R2		X1		X2		Xm		
0.2880		0.2300		1.0850		1.1460		35.0740		

Speed -Torque Curve

