

## Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	230/460 V
Current	14.4/7.2 A	Speed	690 rpm
Service Factor	1	Phase	3
Efficiency	78.5 %	Power Factor	49.8
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Frame	254T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	309	Opp Drive End Bearing Size	207
UL	Recognized	CSA	Y
IP Code	43	Number of Speeds	1

## Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	10	Rotation	Reversible
Resistance Main	3.19 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7308	Outline Drawing	B-SS203005-1175

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/02/2022