

Nameplate Specifications

Phase	3	Output HP	15 & 10 Hp
Output KW	11.2 & 7.5 kW	Voltage	230/460 & 190/380 V
Speed	1745 & 1465 rpm	Service Factor	1.0 & 1.0
Frame	254TC	Enclosure	Explosion Proof Fan cooled
Thermal Protection	No Protection	Efficiency	86.5 & 88 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	40/19.9 & 33/16.5 A	Power Factor	81
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	F
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6207
UL	Listed	CSA	Y
CE	N	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.812 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Overall Length	24.19 in
Frame Length	11.75 in	Shaft Diameter	1.625 in
Shaft Extension	4 in	Assembly/Box Mounting	F1 ONLY
Outline Drawing	B-SS203008-1175	Connection Drawing	A-EE7308T