

Nameplate Specifications

Output HP	15 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	230 V
Current	59.5 A	Speed	1755 rpm
Service Factor	1	Phase	1
Efficiency	86.5 %	Power Factor	94.5
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	D
Frame	256T	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Fixed Clockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	24.06 in
Frame Length	15.45 in	Shaft Diameter	1.625 in
Shaft Extension	5.19 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	A-EE9048PD	Outline Drawing	A-SS88588-1545