

Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	230 V
Current	12.4 A	Speed	3475 rpm
Service Factor	1	Phase	1
Efficiency	81.5 %	Power Factor	96
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Frame	145TY	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	205	Opp Drive End Bearing Size	203
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Fixed Clockwise
Resistance Main	0 Ohms	Mounting	DELTA TABLESAW 30 DEGREE
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1-SPCL-DELTA
Outline Drawing	B-104186-956	Connection Drawing	A-102006-103

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022