

Nameplate Specifications

Phase	3	Output HP	7.50 Hp
Output KW	5.6 kW	Voltage	460 V
Speed	860 rpm	Service Factor	1
Frame	256T	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Efficiency	85 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	12.0 A	Power Factor	68
Duty	60 Minute	Insulation Class	H
Design Code	A	KVA Code	G
Drive End Bearing Size	309	Opp Drive End Bearing Size	309
UL	No	CSA	Y
IP Code	43	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	8	Rotation	Reversible
Resistance Main	1.34 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS203673-1350	Connection Drawing	A-EE7300T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024