

Nameplate Specifications

Phase	3	Output HP	10,5 Hp
Output KW	7.5 kW	Voltage	460 V
Speed	3525,1775 rpm	Service Factor	1.15
Frame	254T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	81.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	12.8,6.8 A	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	1CT	KVA Code	G
Drive End Bearing Size	309	Opp Drive End Bearing Size	207
UL	Recognized	CSA	Y
IP Code	43	Number of Speeds	2

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2/4	Rotation	Reversible
Resistance Main	1.59 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	W7
Outline Drawing	B-SS203675-1175	Connection Drawing	A-EE7324

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024