

### Nameplate Specifications

|                        |                     |                            |                     |
|------------------------|---------------------|----------------------------|---------------------|
| Phase                  | 3                   | Output HP                  | 10 & 4.44 Hp        |
| Output KW              | 7.5 & 3.3 kW        | Voltage                    | 200-230 & 200-230 V |
| Speed                  | 1785 & 1185 rpm     | Service Factor             | 1.15 & 1.15         |
| Frame                  | 256T                | Enclosure                  | Drip Proof          |
| Thermal Protection     | No Protection       | Efficiency                 | 89.5 & 88.5 %       |
| Ambient Temperature    | 40 °C               | Frequency                  | 60 & 60 Hz          |
| Current                | 32-28 & 13.5-12.5 A | Power Factor               | 74.5                |
| Duty                   | Continuous          | Insulation Class           | F                   |
| Design Code            | 2VT                 | KVA Code                   | M                   |
| Drive End Bearing Size | 6309                | Opp Drive End Bearing Size | 6208                |
| UL                     | Recognized          | CSA                        | Y                   |
| CE                     | Y                   | IP Code                    | 22                  |
| Number of Speeds       | 2                   |                            |                     |

### Technical Specifications

|                       |                             |                    |                 |
|-----------------------|-----------------------------|--------------------|-----------------|
| Electrical Type       | Squirrel Cage Induction Run | Starting Method    | Across The Line |
| Poles                 | 4//6                        | Rotation           | Reversible      |
| Resistance Main       | .2628 Ohms                  | Mounting           | Rigid Base      |
| Motor Orientation     | Horizontal                  | Drive End Bearing  | Ball            |
| Opp Drive End Bearing | Ball                        | Frame Material     | Rolled Steel    |
| Shaft Type            | T                           | Shaft Diameter     | 1.625 in        |
| Assembly/Box Mounting | F1/F2 CAPABLE               |                    |                 |
| Outline Drawing       | SS620685-200                | Connection Drawing | EE7317          |