

Nameplate Specifications

Phase	3	Output HP	10 & 4.44 Hp
Output KW	7.5 & 3.3 kW	Voltage	460 & 460 V
Speed	1780 & 1183 rpm	Service Factor	1.15 & 1.15
Frame	256T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	89.5 & 86 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	12.1 & 6.2 A	Power Factor	83.5
Duty	Continuous	Insulation Class	F
Design Code	2VT	KVA Code	H
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//6	Rotation	Reversible
Resistance Main	1.2412 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.625 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	SS620685-200	Connection Drawing	EE7317