

Nameplate Specifications

Phase	3	Output HP	12.50 Hp
Output KW	9.3 kW	Voltage	230/460 V
Speed	1785 rpm	Service Factor	1
Frame	256TCV	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermostat	Efficiency	89.5 %
Ambient Temperature	19 °C	Frequency	60 Hz
Current	41.0/20.5 A	Power Factor	62.5
Duty	Continuous	Insulation Class	F
Design Code	A	KVA Code	P
Drive End Bearing Size	309	Opp Drive End Bearing Size	210
CSA	Y	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.3 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS203641-1225	Connection Drawing	A-EE7308T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024