

Nameplate Specifications

Output HP	13.50 Hp	Output KW	10.1 kW
Frequency	60 Hz	Voltage	460 V
Current	16.5 A	Speed	1772 rpm
Service Factor	1.15	Phase	3
Efficiency	93 %	Power Factor	82
Duty	Continuous	Insulation Class	H
Design Code	A	KVA Code	L
Frame	256TC	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Ambient Temperature	45 °C
Drive End Bearing Size	309	Opp Drive End Bearing Size	309
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.51 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 1000:1		
Connection Drawing	A-EE7300T	Outline Drawing	B-SS203793-1225

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/02/2022