

### Nameplate Specifications

Phase	3	Output HP	10 & 4.44 Hp
Output KW	7.5 & 3.3 kW	Voltage	460 & 460 V
Speed	1760 & 1175 rpm	Service Factor	1.15 & 1.15
Frame	256T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	87.5 & 83.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	12 & 6.5 A	Power Factor	88.2
Duty	Continuous	Insulation Class	B
Design Code	2VT	KVA Code	H
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	2		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//6	Rotation	Reversible
Resistance Main	1.5 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	22.32 in
Frame Length	15.45 in	Shaft Diameter	1.625 in
Shaft Extension	4.19 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7317	Outline Drawing	A-SS86503-1545