

PRODUCT INFORMATION PACKET



Model No: 256TTDX8938

Catalog No: M818

20 HP Vertical Pump Motor, 3 phase, 1800 RPM, 230/460 V, 256HPV Frame, ODP
Vertical Pump Motors

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E




Nameplate Specifications

Output HP	20 Hp	Output KW	14.9 kW
Frequency	60 Hz	Voltage	230/460 V
Current	53.0/26.5 A	Speed	1750 rpm
Service Factor	1.15	Phase	3
Efficiency	88.5 %	Power Factor	79.2
Duty	Continuous	Insulation Class	B
Design Code	B	KVA Code	G
Frame	256HPV	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications


Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	0.5 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	HP	Overall Length	24.30 in
Frame Length	15.15 in	Shaft Diameter	1.630 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1/F2 Capable
Connection Drawing	A-EE7308	Outline Drawing	A-SS86538-1515

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021



DASH	FR.	C	BV	AG
1340	254HP	22.55	13.93	19.80
1515	254/256HP	24.30	15.68	21.55

1. NAMEPLATE TO BE READ FROM SHAFT EXT. END OF MOTOR.
2. BOX CAN BE MOUNTED IN 90° STEPS.

				TOLERANCES UNLESS SPECIFIED			DRAWN KL 11-24-1993			
8	UPDATED DRAWING	TJW 04/27/2007		DEC.	INCHES		CHK ML 11-29-1993			
7	REDRAWN IN AUTOCAD	TAT 07-22-2004	ML	.X	±.1		APPD DRN 11-29-1993			
6	CLARIFIED REVISON HISTORY AND BOX ROT. CN28427	CAV 02-17-2000		.XX	±.03		SCALE 1=5			
5	UPDATED CONDUIT BOX CN 28427	TJB 01-31-2000		.XXX	±.005	TITLE OUTLINE 250HP FR. – BB – TS – 'P' BASE	REF			
4	–1515 WAS FOR 256HP FR. ONLY CN 18683	KL 10-11-1994		.XXXX	±.0005	MAT'L.	FMF			
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"	FINISH	PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE ss86538	SIZE	DRAWING NO.	PAGE	OF	REV.
			DIST LB			A	SS86538			8



NO.	REVISION	BY & DATE	CHK	ANG	TOLERANCES UNLESS SPECIFIED	FINISH	SIZE	DRAWING NO.	PAGE	OF	REV.
5	CHG TO REGAL LOGO	SL 09/10/2015	AB	DEC.	INCHES						
4	REVISED IEC NOTATIONS	MSG 11/15/2011	CMN	.X	±.1						
3	ADDED IEC NOTATIONS... (U1), (V1) ETC. MU95194	MSG 5/10/2010	MJS	.XX	±.02						
2	ADDED THE OPTIONAL CORD CONNECTION MU46318	RDH 04/24/2003	DRS	.XXX	±.005						
1	REDRAWN	RM 11/20/1990		.XXXX	±.0005						
					±7'30"						
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT						RFP	CAD FILE ee7308				
						DIST WP		A	EE7308		5