

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 20 Hp | Output KW | 14.9 kW |
| Frequency | 60 Hz | Voltage | 230/460 V |
| Current | 47.0/23.5 A | Speed | 3510 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Efficiency | 90.2 % | Power Factor | 87.5 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | G |
| Frame | 256TC | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6309 | Opp Drive End Bearing Size | 6207 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 43 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Across The Line |
| Poles | 2 | Rotation | Reversible |
| Resistance Main | .49 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Aluminum |
| Shaft Type | T | Overall Length | 24.99 in |
| Frame Length | 12.75 in | Shaft Diameter | 1.625 in |
| Shaft Extension | 4 in | Assembly/Box Mounting | F1/F2 CAPABLE |
| Connection Drawing | A-EE7308 | Outline Drawing | A-SS84250-1275 |