

Nameplate Specifications

Phase	3	Output HP	20 Hp
Output KW	14.9 kW	Voltage	380 V
Speed	3537 rpm	Service Factor	1.15
Frame	256HP	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	92.4 %
Ambient Temperature	55 °C	Frequency	60 Hz
Current	28.3 A	Power Factor	86
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	309	Opp Drive End Bearing Size	210
UL	Recognized	CSA	Y
IP Code	54	Number of Speeds	1
Hazardous Location	DIVISION 2 T2B		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.394 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	HP	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS203682-1225	Connection Drawing	A-EE7300R

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024