

**Nameplate Specifications**

Phase	3	Output HP	20 Hp
Output KW	14.9 kW	Voltage	415 V
Speed	2930 rpm	Service Factor	1.15
Frame	256T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	90.3 %
Ambient Temperature	50 °C	Frequency	50 Hz
Current	26.1 A	Power Factor	88
Duty	Continuous (S1)	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6210
UL	Recognized	CSA	Y
CE	Y	IP Code	56
Number of Speeds	1	Hazardous Location	ATEX ZONE 2 / ZONE 22

**Technical Specifications**

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.345 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS208264-1225	Connection Drawing	A-EE7300V

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023