

## Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	460 V
Current	14.5 A	Speed	1185 rpm
Service Factor	1	Phase	3
Efficiency	90.2 %	Power Factor	72
Duty	60 Minute	Insulation Class	F
Design Code	INV	KVA Code	L
Frame	284TCV	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Ambient Temperature	40 °C
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6311
UL	Recognized	CSA	Y
CE	Y	IP Code	54
Number of Speeds	1		

## Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	6	Rotation	Reversible
Resistance Main	.508 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	W7
Inverter Load	CONSTANT 2000:1		
Connection Drawing	A-EE7300AK	Outline Drawing	B-SS311575A-1275

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/13/2022