

# PRODUCT INFORMATION PACKET



Model No: 256TTFNA6511  
Catalog No: 256TTFNA6511  
20,3600,TEFC,256HP,3/60/460

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	20 Hp
Output KW	14.9 kW	Voltage	460 V
Speed	3537 rpm	Service Factor	1.15
Frame	256HP	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	92.4 %
Ambient Temperature	55 °C	Frequency	60 Hz
Current	23.4 A	Power Factor	86
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	309	Opp Drive End Bearing Size	210
UL	Recognized	CSA	Y
IP Code	54	Number of Speeds	1
Hazardous Location	DIVISION 2 T2B		

**Technical Specifications**

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.394 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	HP	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS203682-1225	Connection Drawing	A-EE7300R

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024

1. BOX CAN ONLY BE ROTATED CLOCKWISE UP TO 270° FROM ITS ORIGINAL POSITION.
2. NAMEPLATE TO BE READ FROM CONDUIT BOX SIDE OF MOTOR.

3 of 5

ERROR: syntaxerror  
OFFENDING COMMAND: --nostringval--

STACK:



/RS  
-dictionary-  
/Pscript\_WinNT\_Compat  
-dictionary-

SINGLE VOLTAGE THREE PHASE  
MOTOR WITH 2 LEADS OUT FROM  
SPACE HEATERS.

SPACE HEATER


SPACE HEATERS  
CONNECTED IN PARALLEL


SPACE HEATERS CONNECTED  
IN SERIES PARALLEL



VIEW OF TERMINAL END

IF MOTOR HAS  
6 LEADS



				TOLERANCES UNLESS SPECIFIED		REGAL-BELOIT 			DRAWN PGK 08-06-1996			
				DEC.	INCHES				CHK ML 08-07-1996			
				.X	±.1				APPD TB 08-07-1996			
				.XX	±.02				SCALE 1=1			
7	REVISED T1,T2,T3 PER MU65991	CTO 06-08-2005	DD	.XXX	±.005	TITLE CONNECTION DIAGRAM 3ø – SINGLE VOLTAGE			REF			
6	REDRAWN ON CAD CN 22509	PGK 08-07-1996		.XXXX	±.0005				MAT'L.			FMF
NO.	REVISION	BY & DATE	CHK	ANG	±'30"	FINISH			PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE ee7300r			SIZE	DRAWING NO.	PAGE	OF	REV.
			DIST LB					A	EE7300R			7