

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 284TSTDR16003

Catalog No: E1008

XRI® General Purpose General Purpose Motor, 30 & 30 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V,
3600 & 3000 RPM, 284TS Frame, DP



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	3	Output HP	30 & 30 Hp
Output KW	22.4 & 22.4 kW	Voltage	230/460 & 200/400 V
Speed	3535 & 2915 rpm	Service Factor	1.15 & 1.15
Frame	284TS	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	91.7 & 89.5 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	69.0/34.5 & 80.2/40.1 A	Power Factor	88.8
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	F
Drive End Bearing Size	6213	Opp Drive End Bearing Size	6207
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	TS	Overall Length	22.85 in
Shaft Diameter	1.625 in	Shaft Extension	3.25 in
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	18722701-001-S01	Connection Drawing	80022802

REV	ECO	REV BY	DATE	APPD	DATE
B	0003531	K.PALOMO	01-07-09	C.CONTRERAS	01-07-09



NOTES:

- 1- CONDUIT BOX MAY BE ROTATED IN 90° INCREMENTS.
- 2- MOTOR IS SUITABLE FOR FIELD CONVERSION FROM AN F1 TO AN F2 CONDUIT BOX LOCATION.
- 3- MOTOR VENTILATION: AIR INTAKE THROUGH OPENINGS IN THE FACE OF EACH BRACKET AND EXHAUSTED THROUGH THE VENT SLOTS ON EACH END OF THE SHELL.

MOTOR DESCRIPTION:

3 PHASE OPEN DRIPPROOF STEEL SHELL 284TS OR 286TS MOUNTING.
OTHER MOUNTING ORIENTATIONS ARE ACCEPTABLE; HOWEVER WHEN MOUNTED OTHER THAN HORIZONTAL; MOTOR WILL NOT BE DRIPPROOF AS DEFINED BY NEMA.


GEOMETRIC CHARACTERISTICS & SYMBOLS
□ FLATNESS
— STRAIGHTNESS
∠ ANGULARITY
⊥ PERPENDICULARITY (SQUARENESS)
// PARALLELISM
○ ROUNDNESS (CIRCULARITY)
⊘ CYLINDRICITY
△ PROFILE OF ANY SURFACE
△ PROFILE OF ANY LINE
⊕ RUNOUT
⊕ TRUE POSITION
⊕ CONCENTRICITY
= SYMMETRY

UNLESS OTHERWISE SPECIFIED
DIM. TOLERANCES ARE AS FOLLOWS:
INCH ±.1 ±.02 ±.005 ±.0005
mm ±0.5 ±0.13 ±0.013
ANG. ±.50 DEG
REMOVE BURRS & BREAK SHARP EDGES:
INCH .003-.015 mm 0.1-0.4
CORNER FILLETS TO:
INCH .020 mm 0.5
MACHINE SURFACES:
INCH 125 mm 3.2
METRIC DIMS. SHOWN IN [BRACKETS]

DR BY: AJB
APPD: DVB
THIRD ANGLE PROJECTION

01-19-04
01-19-04
EDS DATE EDS DATE
FORMAT REV F
CONFIDENTIAL: THIS DRAWING AND ITS INFORMATION ARE THE EXCLUSIVE AND CONFIDENTIAL PROPERTY OF A.O. SMITH CORP. AND ARE NOT TO BE DISCLOSED, DUPLICATED, DISTRIBUTED OR OTHERWISE USED WITHOUT THE WRITTEN CONSENT OF A.O. SMITH CORP.
-ALL RIGHTS RESERVED.
ASME Y14.5M 1994

ACSmith
Innovation has a name.
ELECTRICAL PRODUCTS COMPANY
A DIVISION OF A. O. SMITH CORPORATION
DESCRIPTION
OUTLINE
SIZE D DWG NO 18722701-001
SCALE NONE SHEET 1





3- MOTOR VENTILATION: AIR INTAKE THROUGH OPENINGS IN THE FACE OF EACH BRACKET AND EXHAUSTED THROUGH THE VENT SLOTS ON EACH END OF THE SHELL.

MOTOR DESCRIPTION:
3 PHASE OPEN DRIPPROOF STEEL SHELL 284TS OR 286TS MOUNTING.
OTHER MOUNTING ORIENTATIONS ARE ACCEPTABLE; HOWEVER WHEN MOUNTED OTHER
THAN HORIZONTAL; MOTOR WILL NOT BE DRIPPROOF AS DEFINED BY NEMA.

CARACTERÍSTICAS DE GEOMETRIA Y SIMBOLOS ☒ PLANICIDAD ☒ RECTITUD ☒ ANGULARIDAD ☒ PERPENDICULARIDAD (A ESQUADRA) ☒ PARALELISMO ☒ REDONDEO (CIRCULARIDAD) ☒ CILINDRICIDAD ☒ PERFIL DE CUALQUIER SUPERFICIE ☒ PERFIL DE CUALQUIER LINEA ☒ VARIACION ☒ POSICION REAL ☒ CONSISTENCIA ☒ SIMITRIA	A MENOS QUE SE ESPECIFIQUE DE OTRA MANERA, LAS TOLERANCIAS DE LAS DIMS; SON LAS SIGUIENTES: $\begin{matrix} & X & XX & XXX & XXXX \\ PULG & \pm .02 & \pm .005 & \pm .0005 & \end{matrix}$ $\begin{matrix} & mm & \pm 0.5 & \pm 0.13 & \pm 0.013 \end{matrix}$ ANG. ± 50 GRADOS ELIMINAR REBABAS Y ORILLAS FILOSAS DEL BORDE PULG .003-.015 mm 0.1-0.4 FILETEAR ESQUINA: PULG .020 mm 0.5 MAQUINAR SUPERFICIES PULG 1/25 mm 3/2 DIMS METRICAS MOSTRADAS [PARENTESIS]	DIBUJADO POR: AUB APROBADO POR: DVB TERCER ANGLULO DE PROYECCION 	01-19-04 01-19-04 FECHA EDS: EDS DATE REV. FORMATO: F	 ELECTRICAL PRODUCTS COMPANY A DIVISION OF A. O. SMITH CORPORATION DESCRIPCION: OUTLINE TAMAÑO: D NUMERO DE DIBUJO: 18722701-001 ESCALA: NONE HOJA: 1

版本	ECO	编制	日期	批准	日期
B	0003531	K.PALOMO	01-07-09	C.CONTRERAS	01-07-09



- NOTES:
- 1- CONDUIT BOX MAY BE ROTATED IN 90° INCREMENTS.
 - 2- MOTOR IS SUITABLE FOR FIELD CONVERSION FROM AN F1 TO AN F2 CONDUIT BOX LOCATION.
 - 3- MOTOR VENTILATION: AIR INTAKE THROUGH OPENINGS IN THE FACE OF EACH BRACKET AND EXHAUSTED THROUGH THE VENT SLOTS ON EACH END OF THE SHELL.

MOTOR DESCRIPTION:
3 PHASE OPEN DRIPPROOF STEEL SHELL 284TS OR 286TS MOUNTING.
OTHER MOUNTING ORIENTATIONS ARE ACCEPTABLE; HOWEVER WHEN MOUNTED OTHER THAN HORIZONTAL; MOTOR WILL NOT BE DRIPPROOF AS DEFINED BY NEMA.

形位公差 □ 平面度 — 直线度 ∠ 倾斜度 ⊥ 垂直度 ∥ 平行度 ○ 圆度 ⊙ 圆柱度 ⌒ 面轮廓度 ⌒ 线轮廓度 ⌒ 位置度 ⌒ 同轴度 ⌒ 对称度	除另有注明 尺寸公差如下: X XX XXX XXXX 英寸 ±.1 ±.02 ±.005 ±.0005 毫米 ±0.5 ±0.13 ±0.013 角度 ±.50 度 清理毛刺和尖棱 英寸 .003-.015 毫米 0.1-0.4 内圆角 英寸 .020 毫米 0.5 表面粗糙度 英制 125 米制 3.2 米制尺寸显示在[]	绘图: AJB 批准: DVB 第三角投影 图底格式发布日期 EDS DATE 图底格式版本 F	01-19-04 01-19-04 F	名称 OUTLINE	图号 18722701-001	比例 NONE	页号 1
---	---	--	---------------------------	---------------	--------------------	------------	---------



**P.O. BOX 8003
WAUSAU, WI 54401-8003
PH. 715-675-3311**

CERTIFICATION DATA SHEET**CUSTOMER:****ORDER #:****CONN. DIAGRAM:** 80022802**OUTLINE:** 18722701-001**WINDING #:** BIR2T01 3**CUSTOMER PO#:****MODEL #:** 284TSTDR16003 AA**CUSTOMER PART #:****MOUNTING:** F1 ONLY**TYPICAL MOTOR PERFORMANCE DATA**

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
30&30	22.4&22.4	3600	3535&2915	284TS	DP	F	B

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
3	60/50	230/460&200/400	69.0/34.5&80.2/40.1	ACROSS THE LINE	CONTINUOUS	F4	1.15/1.15	40

FULL LOAD EFF:	91.7&89.5	3/4 LOAD EFF:	91.6	1/2 LOAD EFF:	90.2	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	88.8&90.0	3/4 LOAD PF:	88.5	1/2 LOAD PF:	83.4	90.2		SQ CAGE IND RUN

F.L. TORQUE		LOCKED ROTOR AMPS		L.R. TORQUE		B.D. TORQUE		F.L. RISE°C
44.6 LB-FT		388 / 194		141 LB-FT 0 %		266 LB-FT 0 %		42

SOUND PRESSURE @ 3 FT.		SOUND POWER		ROTOR WK^2		MAX. WK^2		SAFE STALL TIME		STARTS / HOUR		APPROX. MOTOR WGT
0 dBA		10 dBA		0 LB-FT^2		0 LB-FT^2		0 SEC.		0		340 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	TS	NONE	NONE	1045 HOT ROLLED (C-204)	ROLLED STEEL
6213	6207						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

PREPARED BY: Dinesh**Suddula DATE:**

03/11/2019 04:24:41 AM

FORM 3531 REV.3 02/07/99

** Subject to change without
notice.