

PRODUCT INFORMATION PACKET

Model No: 284TTDR8097

Catalog No: M815

Other Purpose Motor, 15 HP, 3 Ph, 60 Hz, 230/460 V, 1200 RPM, 284HPV Frame, DP

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E




Nameplate Specifications

Output HP	15 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	230/460 V
Current	42.0/21.0 A	Speed	1165 rpm
Service Factor	1.15	Phase	3
Efficiency	85.5 %	Power Factor	78
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	F
Frame	284HPV	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6210
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications


Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	1.04 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	HP	Overall Length	27.06 in
Frame Length	11.00 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	A-EE7308	Outline Drawing	B-SS28183-1100



NOTE:

- CONDUIT BOX CAN BE ROTATED IN 90° STEPS.
- NAMEPLATE TO BE READ FROM SHAFT EXT. END OF MOTOR

DASH	FRAME	AG	C	BV		
1100	284/6HP	21.31	27.06	11.56		
1250	284/6HP	22.81	28.56	12.31		
1350	284/6HP	23.81	29.56	12.81		

					TOLERANCES UNLESS SPECIFIED			DRAWN NJS 12-29-1999		
				DEC.	INCHES			CHK	ML 12-29-1999	
10	REDRAWN IN AUTOCAD		TAT 07-22-2004	ML	.X	±.1		APPD	GK 12-29-2000	
9	REVISED TO NEC CONDUIT BOX CN 28428	NJS 02-18-2000		.XX	±.03		TITLE OUTLINE-"P" FLG.-NEMA SHAFT EXT. 280 HP FR.-BB-TS-VERT. DR. PR.	SCALE	7=32	
8	ADDED 286 FR. TO DASH 1100 MU28622	MJD 02-10-2000		.XXX	±.005			REF		
7	REDRAWN ON CADD - WAS "A" SIZE	NJS 12-29-1999		.XXXX	±.0005			FMF		
NO.	REVISION	BY & DATE		CHK	ANG	±7'30"	FINISH	PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT							RFP	CAD FILE ss28183	SIZE	DRAWING NO. PAGE OF REV.
							DIST LB	B	SS28183	10



NO.	REVISION	BY & DATE	CHK	ANG	TOLERANCES UNLESS SPECIFIED		RFP	CAD FILE	SIZE	DRAWING NO.	PAGE	OF	REV.
					DEC.	INCHES							
5	CHG TO REGAL LOGO	SL 09/10/2015	AB		DEC.	INCHES							
4	REVISED IEC NOTATIONS	MSG 11/15/2011	CMN	.X		±.1							
3	ADDED IEC NOTATIONS... (U1), (V1) ETC. MU95194	MSG 5/10/2010	MJS	.XX		±.02							
2	ADDED THE OPTIONAL CORD CONNECTION MU46318	RDH 04/24/2003	DRS	.XXX		±.005							
1	REDRAWN	RM 11/20/1990		.XXXX		±.0005							
						±7'30"							
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT								CAD FILE ee7308	A	EE7308			5