

### Nameplate Specifications

|                        |                                |                            |                             |
|------------------------|--------------------------------|----------------------------|-----------------------------|
| Phase                  | 3                              | Output HP                  | 15 & 10 Hp                  |
| Output KW              | 11.2 & 11.0 kW                 | Voltage                    | 208-230/460 & 190/380 V     |
| Speed                  | 1180 & 975 rpm                 | Service Factor             | 1.15 & 1.15                 |
| Frame                  | 284T                           | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection                  | Efficiency                 | 90.2 & 87.5 %               |
| Ambient Temperature    | 40 °C                          | Frequency                  | 60 & 50 Hz                  |
| Current                | 44.7 - 40.4/20.2 & 47.0/23.5 A | Power Factor               | 77.1                        |
| Duty                   | Continuous                     | Insulation Class           | F                           |
| Design Code            | B                              | KVA Code                   | G                           |
| Drive End Bearing Size | 6311                           | Opp Drive End Bearing Size | 6309                        |
| UL                     | Recognized                     | CSA                        | Y                           |
| CE                     | Y                              | IP Code                    | 43                          |
| Number of Speeds       | 1                              |                            |                             |

### Technical Specifications

|                    |                             |                       |                 |
|--------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type    | Squirrel Cage Induction Run | Starting Method       | Across The Line |
| Poles              | 6                           | Rotation              | Reversible      |
| Mounting           | Rigid Base                  | Motor Orientation     | Horizontal      |
| Drive End Bearing  | Ball                        | Opp Drive End Bearing | Ball            |
| Frame Material     | Cast Iron                   | Shaft Type            | T               |
| Overall Length     | 27.83 in                    | Shaft Diameter        | 1.875 in        |
| Shaft Extension    | 4.87 in                     | Assembly/Box Mounting | F1/F2 CAPABLE   |
| Connection Drawing | A-EE7308K                   | Outline Drawing       | 16953960ME-284T |