

Nameplate Specifications

Phase	3	Output HP	15,3.75 Hp
Output KW	11.2 kW	Voltage	400 V
Speed	1780,886 r/min	Service Factor	1.15
Frame	284T	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Efficiency	91 %
Ambient Temperature	50 °C	Frequency	60 Hz
Current	21.3,7.7 A	Power Factor	84
Duty	Continuous	Insulation Class	H
Design Code	2VT	KVA Code	J
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6210
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//8	Rotation	Reversible
Resistance Main	.702 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	SS311162-1275	Connection Drawing	A-EE7317

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/08/2025