

# PRODUCT INFORMATION PACKET

**marathon®**  
Motors

Model No: 286TSTFNA6501

Catalog No: E608

30 HP Severe Duty Motor, 3 phase, 3600 RPM, 460 V, 286TS Frame, TEFC  
Severe Duty Motors



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

**RegalRexnord**


**Nameplate Specifications**

|                        |                       |                            |                                    |
|------------------------|-----------------------|----------------------------|------------------------------------|
| Output HP              | <b>30 Hp</b>          | Output KW                  | <b>22.4 kW</b>                     |
| Frequency              | <b>60 Hz</b>          | Voltage                    | <b>460 V</b>                       |
| Current                | <b>33.5 A</b>         | Speed                      | <b>3555 rpm</b>                    |
| Service Factor         | <b>1.15</b>           | Phase                      | <b>3</b>                           |
| Efficiency             | <b>93 %</b>           | Power Factor               | <b>89.5</b>                        |
| Duty                   | <b>Continuous</b>     | Insulation Class           | <b>F</b>                           |
| Design Code            | <b>B</b>              | KVA Code                   | <b>G</b>                           |
| Frame                  | <b>286TS</b>          | Enclosure                  | <b>Totally Enclosed Fan Cooled</b> |
| Thermal Protection     | <b>No</b>             | Ambient Temperature        | <b>40 °C</b>                       |
| Drive End Bearing Size | <b>6311</b>           | Opp Drive End Bearing Size | <b>6210</b>                        |
| UL                     | <b>Recognized</b>     | CSA                        | <b>Y</b>                           |
| CE                     | <b>Y</b>              | IP Code                    | <b>54</b>                          |
| Hazardous Location     | <b>DIVISION 2 T2B</b> | Number of Speeds           | <b>1</b>                           |

**Technical Specifications**

|                       |                                     |                       |                         |
|-----------------------|-------------------------------------|-----------------------|-------------------------|
| Electrical Type       | <b>Squirrel Cage Inverter Rated</b> | Starting Method       | <b>Line Or Inverter</b> |
| Poles                 | <b>2</b>                            | Rotation              | <b>Reversible</b>       |
| Resistance Main       | <b>.3 Ohms</b>                      | Mounting              | <b>Rigid Base</b>       |
| Motor Orientation     | <b>Horizontal</b>                   | Drive End Bearing     | <b>Ball</b>             |
| Opp Drive End Bearing | <b>Ball</b>                         | Frame Material        | <b>Cast Iron</b>        |
| Shaft Type            | <b>TS</b>                           | Overall Length        | <b>26.56 in</b>         |
| Frame Length          | <b>14.25 in</b>                     | Shaft Diameter        | <b>1.625 in</b>         |
| Shaft Extension       | <b>3.45 in</b>                      | Assembly/Box Mounting | <b>F1/F2 CAPABLE</b>    |
| Outline Drawing       | <b>B-SS311136-1425</b>              | Connection Drawing    | <b>A-EE7300U</b>        |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021



|      |           |                   |                   |                  |                   |                  |
|------|-----------|-------------------|-------------------|------------------|-------------------|------------------|
| 1275 | 284TS     | 25.06<br>[636.53] | 12.50<br>[317.50] | ---              | 9.50<br>[241.30]  | 4.75<br>[120.65] |
| 1425 | 284/286TS | 26.56<br>[674.61] | 13.00<br>[330.20] | 9.50<br>[241.30] | 11.00<br>[279.40] | 5.50<br>[139.64] |
| DASH | FRAME     | C                 | B                 | 2F               | 2FF               | BS               |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                     |                    |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|--------------------|
| DRAWING REVISION<br>F                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | REVISION BY<br>MSG  | DATE<br>11-10-2015 |
| ECO<br>ECO-0088479                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | APPROVED BY<br>TVUE | DATE<br>11-11-2015 |
| ECO DESCRIPTION<br><b>UPDATED TO CURRENT STANDARDS</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                     |                    |
| COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.<br>PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF<br>REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY<br>INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED,<br>BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED<br>TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT<br>AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL<br>BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN<br>RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. |                     |                    |

**TOLERANCES UNLESS OTHERWISE SPECIFIED:**

| <u>DEC.</u> | <u>INCH</u> | <u>mm</u> | <u>ANGLE</u> |
|-------------|-------------|-----------|--------------|
| .X          | ±0.1        | [±2.5]    | ±7° 30'      |
| .XX         | ±0.03       | [±0.76]   |              |
| .XXX        | ±0.005      | [±0.127]  |              |
| .XXXX       | ±0.0005     | [±0.0127] |              |

REMOVE BURRS & BREAK SHARP  
EDGES: .003/.015 [.076/.381] X 45°  
CORNER FILLETS: R.02 [.51]  
MACHINED SURFACES: 200 5.1  
INCH mm  
mm SHOWN IN [BRACKETS]



**REGAL**™ Regal Beloit America, Inc.

## IF MOTOR HAS 9 LEADS



## IF MOTOR HAS 6 LEADS



A-9806 DECAL IF CALLED FOR

## IF MOTOR HAS 12 LEADS



VIEW OF TERMINAL END

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                    |                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                       |                                                                   |                                                                              |  |                 |                |  |  |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------|------------------------------------------------------------------------------|--|-----------------|----------------|--|--|--|
| DRAWING REVISION<br>L                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | REVISION BY<br>AJW | DATE<br>05-04-2015 | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><div><div>DEC.</div><div>INCH.</div><div>mm</div></div> <div>ANGLE</div> <div>±7' 30"</div> <div>.X ±0.1 [±2.5]</div> <div>.XX ±0.02 [±0.51]</div> <div>XXX ±0.005 [±0.127]</div> <div>.XXXX ±0.0005 [±0.0127]</div> <div>REMOVE BURRS &amp; BREAK SHARP<br/>EDGES: .003/.015 [.076/.381] X 45°</div> <div>CORNER FILLETS: R.02 [.51]</div> <div>MACHINED SURFACES: 200</div> <div>INCH</div> <div>5.1</div> <div>mm</div> <div>mm SHOWN IN [BRACKETS]</div> | DRAWN BY<br>DRS                                                                       | <div><div>REGAL™</div><div>Regal Beloit America, Inc.</div></div> | DESCRIPTION<br><div>CONN DIAGRAM-EXTERNAL</div> <div>3Ø SINDLE VOLTAGE</div> |  |                 |                |  |  |  |
| ECO<br>ECO-0077067                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | APPROVED BY<br>EWH | DATE<br>05-05-2015 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | DATE<br>09-27-1996                                                                    |                                                                   |                                                                              |  |                 |                |  |  |  |
| ECO DESCRIPTION<br>UPDATED TO SOLIDWORKS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |                    |                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | APPROVED BY<br>GK                                                                     | MATERIAL                                                          |                                                                              |  |                 | PROCESS/FINISH |  |  |  |
| COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.<br>PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF<br>REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY<br>INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED,<br>BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED<br>TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT<br>AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL<br>BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN<br>RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. |                    |                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | DATE<br>09-30-1996                                                                    |                                                                   |                                                                              |  |                 |                |  |  |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                    |                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                       |                                                                   |                                                                              |  |                 | REFERENCE      |  |  |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                    |                    | THIRD ANGLE<br>PROJECTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |  | SIZE<br>A                                                         | DRAWING NUMBER<br>EE7300U                                                    |  | SHEET<br>1 OF 1 |                |  |  |  |

## CERTIFICATION DATA SHEET

Model#: 286TSTFNA6501 BB  
 CONN. DIAGRAM: A-EE7300U  
 OUTLINE: B-SS311136-1425

WINDING#: K2862155 NONE 2  
 ASSEMBLY: F1/F2 CAPABLE

## TYPICAL MOTOR PERFORMANCE DATA

| HP | KW   | SYNC. RPM | F.L. RPM | FRAME | ENCLOSURE | KVA CODE | DESIGN |
|----|------|-----------|----------|-------|-----------|----------|--------|
| 30 | 22.4 | 3600      | 3555     | 286TS | TEFC      | G        | B      |

| PH | Hz | VOLTS | FL AMPS | START TYPE          | DUTY       | INSL | S.F  | AMB°C | ELEVATION |
|----|----|-------|---------|---------------------|------------|------|------|-------|-----------|
| 3  | 60 | 460   | 33.5    | LINE OR<br>INVERTER | CONTINUOUS | F3   | 1.15 | 40    | 3300      |

|                    |                    |                  |          |                   |              |
|--------------------|--------------------|------------------|----------|-------------------|--------------|
| FULL LOAD EFF: 93  | 3/4 LOAD EFF: 93.6 | 1/2 LOAD EFF: 93 | GTD. EFF | ELEC. TYPE        | NO LOAD AMPS |
| FULL LOAD PF: 89.5 | 3/4 LOAD PF: 87    | 1/2 LOAD PF: 81  | 92.4     | SQ CAGE INV RATED | 9.5          |

|             |                   |              |               |             |
|-------------|-------------------|--------------|---------------|-------------|
| F.L. TORQUE | LOCKED ROTOR AMPS | L.R. TORQUE  | B.D. TORQUE   | F.L. RISE°C |
| 44.5 LB-FT  | 217               | 63 LB-FT 142 | 123 LB-FT 275 | 65          |

|                           |             |             |            |                 |                 |                      |
|---------------------------|-------------|-------------|------------|-----------------|-----------------|----------------------|
| SOUND PRESSURE<br>@ 3 FT. | SOUND POWER | ROTOR WK^2  | MAX. WK^2  | SAFE STALL TIME | STARTS<br>/HOUR | APPROX. MOTOR<br>WGT |
| 72 dBA                    | 82 dBA      | 2.7 LB-FT^2 | 35 LB-FT^2 | 20 SEC.         | 2               | 450 LBS.             |

## \*\*\* SUPPLEMENTAL INFORMATION \*\*\*

| DE BRACKET<br>TYPE | ODE BRACKET<br>TYPE | MOUNT<br>TYPE | ORIENTATION | SEVERE<br>DUTY         | HAZARDOUS<br>LOCATION | DRIP<br>COVER | SCREENS | PAINT        |
|--------------------|---------------------|---------------|-------------|------------------------|-----------------------|---------------|---------|--------------|
| STANDARD           | STANDARD            | RIGID         | HORIZONTAL  | PREMIUM<br>SEVERE DUTY | DIVISION 2 T2B        | FALSE         | NONE    | BLUE (EPOXY) |

| BEARINGS |      | GREASE     | SHAFT TYPE | SPECIAL DE | SPECIAL ODE | SHAFT<br>MATERIAL          | FRAME<br>MATERIAL |
|----------|------|------------|------------|------------|-------------|----------------------------|-------------------|
| DE       | OPE  |            |            |            |             |                            |                   |
| BALL     | BALL |            |            |            |             |                            |                   |
| 6311     | 6210 | POLYREX EM | TS         | NONE       | NONE        | 1045 HOT<br>ROLLED (C-204) | CAST IRON         |

| THERMO-PROTECTORS |            |          |          | THERMISTORS | CONTROL | SPACE /n HEATERS |
|-------------------|------------|----------|----------|-------------|---------|------------------|
| THERMOSTATS       | PROTECTORS | WDG RTDs | BRG RTDs |             |         |                  |
| NONE              | NOT        | NONE     | NONE     | NONE        | FALSE   | NONE VOLTS       |

If Inverter equals NONE, contact factory for further information

|                                 |                                       |  |        |  |         |  |
|---------------------------------|---------------------------------------|--|--------|--|---------|--|
| *<br>N<br>O<br>T<br>E<br>S<br>* | INVERTER TORQUE: CONSTANT 20:1        |  |        |  |         |  |
|                                 | INV. HP SPEED RANGE: 1.5 X BASE SPEED |  |        |  |         |  |
|                                 | ENCODER: NONE                         |  |        |  |         |  |
|                                 | NONE NONE                             |  |        |  |         |  |
|                                 | NONE NONE PPR                         |  |        |  |         |  |
|                                 | BRAKE: NONE NONE                      |  |        |  |         |  |
|                                 | NONE P/N NONE                         |  |        |  |         |  |
|                                 | NONE NONE                             |  |        |  |         |  |
|                                 | NONE FT-LB                            |  | NONE V |  | NONE Hz |  |

DATE: 06/21/2017 10:40:24 AM  
 FORM 3531 REV.3 02/07/99  
 \*\* Subject to change without notice.

## Data Sheet

Date: 6/29/2017

Customer: \_\_\_\_\_

Attention: \_\_\_\_\_

Submitted by: FAREEDA DUDEKULA



286TSTFNA6501

Submittal

Data @ 460 V

## Motor Load Data

| Load           | 0%   | 25%  | 50%  | 75%  | 100% | 115%  | 125% | LR   |  |
|----------------|------|------|------|------|------|-------|------|------|--|
| Current (Amps) | 9.5  | 12.7 | 18.5 | 26.0 | 33.5 | 38.5  | 42.0 | 217  |  |
| Torque (ft-lb) | 0.00 | 11.0 | 22.0 | 33.0 | 44.5 | 51.0  | 56.0 | 63.0 |  |
| RPM            | 3600 | 3590 | 3578 | 3565 | 3555 | 3,547 | 3542 | 0    |  |
| Efficiency (%) |      | 89.5 | 93.0 | 93.6 | 93.0 | 93.0  | 92.4 |      |  |
| P.F. (%)       | 6.5  | 61.5 | 81.0 | 87.0 | 89.5 | 90.0  | 90.5 | 32.0 |  |

## Motor Speed Data

|                                                                                                                                    | LR   | Pull-Up | BD   | Rated  | Idle | Information Block           |                         |       |  |  |
|------------------------------------------------------------------------------------------------------------------------------------|------|---------|------|--------|------|-----------------------------|-------------------------|-------|--|--|
| Speed (RPM)                                                                                                                        | 0    | 1800    | 3400 | 3555   | 3600 | HP                          | 30.0                    |       |  |  |
| Current (Amps)                                                                                                                     | 217  | 195     | 138  | 33.5   | 9.5  | Sync. RPM                   | 3600                    |       |  |  |
| Torque (ft-lb)                                                                                                                     | 63.0 | 56.0    | 123  | 44.5   | 0.00 | Frame                       | 286                     |       |  |  |
| <div><div>— Efficiency (%) — P.F. (%) — Current (Amps)</div><div>EFFICIENCY (%) P.F. (%) CURRENT (AMPS)</div><div>LOAD</div></div> |      |         |      |        |      | Enclosure                   | TEFC                    |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Construction                | TFN                     |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Voltage                     | 460 V                   |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Frequency                   | 60 Hz                   |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Design                      | A                       |       |  |  |
|                                                                                                                                    |      |         |      |        |      | LR Code letter              | G                       |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Service Factor              | 1.15                    |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Temp Rise @ FL              | 65 ° C                  |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Duty                        | CONT                    |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Ambient                     | 40 ° C                  |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Elevation                   | 1,000 feet              |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Rotor/Shaft wk <sup>2</sup> | 2.70 Lb-Ft <sup>2</sup> |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Ref Wdg                     | K2862155 NONE           |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Sound Pressure @ 1M         | 72 dBA                  |       |  |  |
|                                                                                                                                    |      |         |      |        |      | VFD Rating                  | CONSTANT 20:1           |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Outline Dwg                 | B-SS311136-1425         |       |  |  |
|                                                                                                                                    |      |         |      |        |      | Conn. Diag                  | A-EE7300U               |       |  |  |
| Additional Specifications:                                                                                                         |      |         |      |        |      |                             |                         |       |  |  |
| 0                                                                                                                                  |      |         |      |        |      |                             |                         |       |  |  |
| 0                                                                                                                                  |      |         |      |        |      |                             |                         |       |  |  |
| EQUIV CKT (OHMS / PHASE)                                                                                                           |      |         |      |        |      |                             |                         |       |  |  |
| R1                                                                                                                                 |      | R2      |      | X1     |      | X2                          |                         | Xm    |  |  |
| 0.1970                                                                                                                             |      | 0.1040  |      | 0.7940 |      | 0.6050                      |                         | ##### |  |  |

## Speed -Torque Curve

