

Nameplate Specifications

Phase	3	Output HP	25 Hp
Output KW	18.7 kW	Voltage	460 V
Speed	1478 rpm	Service Factor	1
Frame	326TV	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Efficiency	93 %
Ambient Temperature	40 °C	Frequency	50 Hz
Current	32.5 A	Power Factor	78
Duty	Continuous	Insulation Class	H
Design Code	INV	KVA Code	J
Drive End Bearing Size	312	Opp Drive End Bearing Size	311
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.128 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	W8
Outline Drawing	B-SS312160-1625	Connection Drawing	A-EE7300T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023