

Nameplate Specifications

Phase	3	Output HP	50 Hp
Output KW	37.3 kW	Voltage	480 V
Speed	1760 rpm	Service Factor	1.15
Frame	326Y	Enclosure	Drip Proof
Thermal Protection	Thermostat	Efficiency	90.2 %
Ambient Temperature	60 °C	Frequency	60 Hz
Current	60.5 A	Power Factor	83
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	F
Drive End Bearing Size	312	Opp Drive End Bearing Size	311
UL	No	CSA	Y
IP Code	22	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.198 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Special Extension Both Sides	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS300497-1092	Connection Drawing	A-EE7300T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/09/2024