

Nameplate Specifications

Phase	3	Output HP	62.50 Hp
Output KW	47.0 kW	Voltage	480 V
Speed	1760 rpm	Service Factor	1
Frame	326TCVZ	Enclosure	Open Enclosed
Thermal Protection	Thermostat	Efficiency	90.2 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	83.5 A	Power Factor	74.5
Duty	60 Minute	Insulation Class	H
Design Code	A	KVA Code	D
Drive End Bearing Size	6312	Opp Drive End Bearing Size	6311
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.15 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Special Extension Both Sides	Assembly/Box Mounting	W8
Outline Drawing	B-SS300497-1092	Connection Drawing	A-EE7300T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/09/2024