

Nameplate Specifications

Output HP	15 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	460-480 V
Current	21.5-21.5 A	Speed	868 rpm
Service Factor	1	Phase	3
Efficiency	86.5 %	Power Factor	76
Duty	60 Minute	Insulation Class	F
Design Code	A	KVA Code	H
Frame	326TCZ	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	22218	Opp Drive End Bearing Size	22218
UL	Recognized	CSA	Y
CE	Y	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	8	Rotation	Reversible
Resistance Main	.455 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Roller (Spherical)
Opp Drive End Bearing	Roller (Spherical)	Frame Material	Cast Iron
Shaft Type	Special Extension Both Sides	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7300	Outline Drawing	B-SS350630-1625

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/02/2022