

# PRODUCT INFORMATION PACKET



Model No: 364UHTS18531  
Catalog No: 364UHTS18531  
40,1800,TENV,364UCV,3/60/460

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	40 Hp
Output KW	30.0 kW	Voltage	460 V
Speed	1782 rpm	Service Factor	1
Frame	364UCV	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	48.0 A	Power Factor	82.5
Duty	30 Minute	Insulation Class	H
Design Code	A	KVA Code	J
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6312
UL	No	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.115 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	U	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS554609-1450	Connection Drawing	A-EE7300AK


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/05/2024




# P1 AND P2 PROTECTORS TO VOLTAGE CONTROL

TO REVERSE ROTATION:  
INTERCHANGE ANY TWO  
LINE LEAD CONNECTIONS.

PROTECTORS  
CONNECTED  
IN SERIES.



IF MOTOR OR GENERATOR  
HAS 6 LEADS



A-9806 DECAL

VIEW OF TERMINAL END

DRAWING REVISION J	REVISION BY J. OTTO	DATE 04-13-2017	TOLERANCES UNLESS OTHERWISE SPECIFIED: <div><div>DEC.</div><div>INCH</div><div>mm</div><div>ANGLE</div></div> <div><div>.X</div><div>±0.1</div><div>[±2.5]</div><div>±7° 30"</div></div> <div><div>.XX</div><div>±0.02</div><div>[±0.51]</div></div> <div><div>XXX</div><div>±0.005</div><div>[±0.127]</div></div> <div><div>.XXXX</div><div>±0.0005</div><div>[±0.0127]</div></div> <div>REMOVE BURRS &amp; BREAK SHARP EDGES: .003/.015 [.076/.381] CORNER FILLETS: .02 [.51] MACHINED SURFACES: 200 INCH 5.1 mm mm SHOWN IN [BRACKETS]</div>				DRAWN BY MJD	<div><div>REGAL™</div><div>Regal Beloit America, Inc.</div></div>	
ECO ECO-0121568	APPROVED BY T. VUE	DATE 04-18-2017					DATE 06-24-2014		
ECO DESCRIPTION ADDED IEC NOTATIONS			DESCRIPTION CONN DIAGRAM-INTERNAL SINGLE VOLT-3Ø MOTOR						
<div>COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.</div>			APPROVED BY TB	MATERIAL		PROCESS/FINISH			
			DATE 07-06-1998						
			REFERENCE	SIZE A		DRAWING NUMBER EE7300AK		SHEET 1 OF 1	
			THIRD ANGLE PROJECTION	