

### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Phase                  | 3             | Output HP                  | 60 Hp                       |
| Output KW              | 45.0 kW       | Voltage                    | 460 V                       |
| Speed                  | 1780 rpm      | Service Factor             | 1.15                        |
| Frame                  | 364T          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Efficiency                 | 95 %                        |
| Ambient Temperature    | 40 °C         | Frequency                  | 60 Hz                       |
| Current                | 68.0 A        | Power Factor               | 87.2                        |
| Duty                   | Continuous    | Insulation Class           | H                           |
| Design Code            | B             | KVA Code                   | G                           |
| Drive End Bearing Size | 6313          | Opp Drive End Bearing Size | 6213                        |
| UL                     | Listed        | CSA                        | Y                           |
| CE                     | Y             | IP Code                    | 55                          |
| Number of Speeds       | 1             | Hazardous Location         | DIVISION 2 T2B              |

### Technical Specifications

|                       |                              |                    |                             |
|-----------------------|------------------------------|--------------------|-----------------------------|
| Electrical Type       | Squirrel Cage Inverter Rated | Starting Method    | Line Or Inverter            |
| Poles                 | 4                            | Rotation           | Reversible                  |
| Resistance Main       | .104 Ohms                    | Mounting           | Rigid Base                  |
| Motor Orientation     | Horizontal                   | Drive End Bearing  | Ball                        |
| Opp Drive End Bearing | Ball                         | Frame Material     | Cast Iron                   |
| Shaft Type            | T                            | Shaft Diameter     | 2.375 in                    |
| Assembly/Box Mounting | F1/F2 CAPABLE                | Inverter Load      | CONSTANT 10:1/VARIABLE 20:1 |
| Outline Drawing       | SS557662-100                 | Connection Drawing | EE7300U                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2024