



**Nameplate Specifications**

Phase	3	Output HP	75 Hp
Output KW	56.0 kW	Voltage	230/460 V
Speed	3560 rpm	Service Factor	1
Frame	365 D	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	93 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	183.0/91.5 A	Power Factor	82
Duty	Continuous	Insulation Class	NONE
Design Code	B	KVA Code	F
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	NONE
UL	No	CSA	Y
CE	N	IP Code	12
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.34 Ohms	Mounting	Round
Motor Orientation	Horizontal	Frame Material	Cast Iron
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	NONE	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/01/2024