

Nameplate Specifications

Phase	3	Output HP	50 Hp
Output KW	37.0 kW	Voltage	230/460 V
Speed	1185 rpm	Service Factor	1
Frame	365TC	Enclosure	Totally Enclosed Blower cooled - Axial
Thermal Protection	Thermostat	Efficiency	93.3 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	114.0/57.0 A	Power Factor	87
Duty	Continuous	Insulation Class	H
Design Code	INV	KVA Code	G
Drive End Bearing Size	6313	Opp Drive End Bearing Size	6213
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	6	Rotation	Reversible
Resistance Main	.191 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Shaft Diameter	2.375 in
Assembly/Box Mounting	F1/F2 CAPABLE	Inverter Load	CONSTANT 2000:1
Outline Drawing	SS621114-200	Connection Drawing	EE7308T