

# PRODUCT INFORMATION PACKET



Model No: 365TTFCD36026  
Catalog No: 365TTFCD36026  
75,1500,TEFC,365T,3/50/380/460

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**



Phase	3	Output HP	75 Hp
Output KW	56.0 kW	Voltage	380/460 V
Speed	1480 rpm	Service Factor	1.15
Frame	365T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	93.6 %
Ambient Temperature	40 °C	Frequency	50 Hz
Current	105.0/86.5 A	Power Factor	86
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6313	Opp Drive End Bearing Size	6213
UL	Listed	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1	Hazardous Location	DIVISION 2 T2B



**Technical Specifications**




Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.07 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Shaft Diameter	2.375 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	SS556999	Connection Drawing	EE7308DD

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/24/2023


4						3					2					1				
DASH NO.	B	C	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME										
100	14.96	33.30	7.00	14.00	-	11.25	5.88	6.12	F1 OR F2	364T										
200	15.94	34.30			11.25	12.25		6.62		364/365T										



DRAWING REVISION C		REVISION BY S SAHOO		REV DATE/© DATE 17/11/2020		DRAWN BY NIV		<div> Regal Beloit America, Inc.</div>				
ECO ECO-0194715		APPROVED BY GNK		DATE 17/11/2020		DATE 25/03/2016						
ECO DESCRIPTION						APPROVED BY SBD		DESCRIPTION				
OUTLINE UPDATED						DATE 25/03/2016		OUTLINE 360T FR-TEFC				
COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.						PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY						
						REFERENCE		MATERIAL		PROCESS/FINISH		
						THIRD ANGLE PROJECTION 		SIZE B		DRAWING NUMBER SS556999		SHEET 1 OF 1



VIEW OF TERMINAL END

				125 √ SURFACE ROUGHNESS UNLESS NOTED OTHERWISE	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL ON XX±      XXX±.005      XXXX±.0005      ANGLES±			
				MATL SPEC				DRAWN BY    AJS    05-01-95
				FINISH	 MARATHON ELECTRIC WAUSAU, WISCONSIN 54401			CHKD BY    ML    05-02-95
I		NEW DRAWING	4275499	AJS				APPD BY
REV	DATE	CHANGE		NAME	PART NAME 3 PHASE CONNECTION DIAGRAM 2Y/1 Δ - 12 LEADS			DRWG NO A - EE7308DD
		PURCHASED		DISTRIBUTION - WA - LB - WP - LM		CADD FILE NO.	EE7308DD	

ERROR: syntaxerror  
OFFENDING COMMAND: --nostringval--

STACK:

148  
/quotedblleft  
147  
/quoteright  
146  
/quoteleft  
145  
/OE  
140  
/guilsinglleft  
139  
/Scaron  
138  
/perthousand  
137  
/circumflex  
136  
/daggerdbl  
135  
/dagger  
134  
/ellipsis  
133  
/quotedblbase  
132  
/florin  
131  
/quotesinglbase  
130  
/bar  
124  
/grave  
96  
/quotesingle  
39  
/dotlessi  
13  
/caron  
12  
/ogonek  
11  
/hungarumlaut  
10  
/cedilla  
9  
/ring  
8  
/dieresis  
7  
/dotaccent  
6  
/breve  
5  
/macron  
4  
/tilde  
3  
/circumflex  
2  
/acute  
1  
/grave  
0  
-mark-  
/ANSIVec  
-dictionary-  
/Pscript\_WinNT\_Compat  
-dictionary-