

PRODUCT INFORMATION PACKET



Model No: 365TTFS7923

Catalog No: M916

75 HP Vertical Pump Motor, 3 phase, 3600 RPM, 230/460 V, 365HPV Frame, TEFC
Vertical Pump Motors

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	75 Hp	Output KW	56.0 kW
Frequency	60 Hz	Voltage	230/460 V
Current	174.0/87.0 A	Speed	3555 rpm
Service Factor	1.15	Phase	3
Efficiency	93 %	Power Factor	86
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	365HPV	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	6312	Opp Drive End Bearing Size	6312
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.076 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	HP	Overall Length	37.61 in
Frame Length	14.50 in	Shaft Diameter	1.625 in
Shaft Extension	4.5 in	Assembly/Box Mounting	F1/F2 Capable
Outline Drawing	B-SS518657-1450	Connection Drawing	A-EE7308K






- NOTES:
1. CONDUIT BOX CAN BE ROTATED IN 90° STEPS
 2. NAMEPLATES TO BE READ FROM CONDUIT BOX SIDE OF MOTOR

(REPLACES B-SS507344)

					<table><tr><td>DRAWING REVISION F</td><td>REVISION BY AJW</td><td>DATE 07-21-2015</td></tr><tr><td>ECO ECO-0081851</td><td>APPROVED BY JHA</td><td>DATE 07-21-2015</td></tr><tr><td colspan="3">ECO DESCRIPTION UPDATED TO CURRENT STANDARDS COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.</td></tr></table>			DRAWING REVISION F	REVISION BY AJW	DATE 07-21-2015	ECO ECO-0081851	APPROVED BY JHA	DATE 07-21-2015	ECO DESCRIPTION UPDATED TO CURRENT STANDARDS COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.			<table><tr><td colspan="3">TOLERANCES UNLESS OTHERWISE SPECIFIED:</td></tr><tr><td>DEC.</td><td>INCH</td><td>mm</td></tr><tr><td>.X</td><td>±0.1</td><td>[±2.5]</td></tr><tr><td>.XX</td><td>±0.03</td><td>[±0.76]</td></tr><tr><td>.XXX</td><td>±0.005</td><td>[±0.127]</td></tr><tr><td>.XXXX</td><td>±0.0005</td><td>[±0.0127]</td></tr><tr><td colspan="3">REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 200 INCH 5.1 mm mm SHOWN IN [BRACKETS]</td></tr></table>			TOLERANCES UNLESS OTHERWISE SPECIFIED:			DEC.	INCH	mm	.X	±0.1	[±2.5]	.XX	±0.03	[±0.76]	.XXX	±0.005	[±0.127]	.XXXX	±0.0005	[±0.0127]	REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 200 INCH 5.1 mm mm SHOWN IN [BRACKETS]			<table><tr><td colspan="2">DRAWN BY TJB</td></tr><tr><td>DATE 08-10-2001</td><td rowspan="3"> Regal Beloit America, Inc.</td></tr><tr><td>APPROVED BY GK</td></tr><tr><td>DATE 08-13-2001</td></tr><tr><td>REFERENCE</td><td>MATERIAL</td><td>PROCESS/FINISH</td></tr><tr><td>THIRD ANGLE PROJECTION </td><td>SIZE B</td><td>DRAWING NUMBER SS518657</td><td>SHEET 1 OF 1</td></tr></table>			DRAWN BY TJB		DATE 08-10-2001	 Regal Beloit America, Inc.	APPROVED BY GK	DATE 08-13-2001	REFERENCE	MATERIAL	PROCESS/FINISH	THIRD ANGLE PROJECTION 	SIZE B	DRAWING NUMBER SS518657	SHEET 1 OF 1
DRAWING REVISION F	REVISION BY AJW	DATE 07-21-2015																																																						
ECO ECO-0081851	APPROVED BY JHA	DATE 07-21-2015																																																						
ECO DESCRIPTION UPDATED TO CURRENT STANDARDS COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.																																																								
TOLERANCES UNLESS OTHERWISE SPECIFIED:																																																								
DEC.	INCH	mm																																																						
.X	±0.1	[±2.5]																																																						
.XX	±0.03	[±0.76]																																																						
.XXX	±0.005	[±0.127]																																																						
.XXXX	±0.0005	[±0.0127]																																																						
REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 200 INCH 5.1 mm mm SHOWN IN [BRACKETS]																																																								
DRAWN BY TJB																																																								
DATE 08-10-2001	 Regal Beloit America, Inc.																																																							
APPROVED BY GK																																																								
DATE 08-13-2001																																																								
REFERENCE	MATERIAL	PROCESS/FINISH																																																						
THIRD ANGLE PROJECTION 	SIZE B	DRAWING NUMBER SS518657	SHEET 1 OF 1																																																					
DASH	FRAME	C	AG	BV																																																				
1450	360HPV	37.61 [955.29]	33.11 [840.99]	13.88 [352.55]																																																				

LOW VOLTAGE

EE7308K

HIGH VOLTAGE

VIEW OF TERMINAL END

			TOLERANCES UNLESS SPECIFIED			 REGAL - BELOIT CORPORATION	DRAWN PGK 06-04-1997		
NO.	REVISION	BY & DATE	CHK	ANG	± 7'30"		CHK	ML	06-05-1997
E	CORRECTED IEC MARKINGS ECD-0111208	WGJ 01-23-2017	EMH	DEC.	INCHES	TITLE CONNECTION DIAGRAM DELTA CON. - 3Ø - 9 LEADS MAT'L. FINISH	APPD	GK	06-15-1997
D	RE-DRAWN WITH REGAL LOGO ECD-0110493	WGJ 09-30-2016	EMH	.X	± .1		SCALE		
8	ADDED IEC DESIGNATIONS MU95020	TJW 4/30/2010	MJS	.XX	± .02		REF		
7	REVISED HIGH VOLTAGE L2 WAS L3 CN52600-354	MRB 09-21-1998		.XXX	± .005		FMF		
6	REDRAWN ON CADD	PGK 06-05-1997		.XXXX	± .0005		PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT						RFP	CAD FILE EE7308K		SIZE
						DIST			A
								DRAWING NO.	PAGE OF
								EE7308K	REV.
								E	