

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 365TTFS16827

Catalog No: U878A

XRI®-SD Severe Duty Motor, 75 & 60 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 & 1500 RPM,
365T Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

Nameplate Specifications


Phase	3	Output HP	75 & 60 Hp
Output KW	56.0 & 45.0 kW	Voltage	230/460 & 190/380 V
Speed	1780 & 1480 rpm	Service Factor	1.15 & 1.15
Frame	365T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	95.4 & 95 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	172/86 & 167/83.5 A	Power Factor	86
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6312
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications



Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.075 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Overall Length	32.51 in
Frame Length	14.50 in	Shaft Diameter	2.375 in
Shaft Extension	6.12 in	Assembly/Box Mounting	F1/F2 Capable
Outline Drawing	B-SS508590-1450	Connection Drawing	A-EE7308K

LOW VOLTAGE

EE7308K



HIGH VOLTAGE



VIEW OF TERMINAL END

				TOLERANCES UNLESS SPECIFIED		 REGAL - BELOIT CORPORATION		DRAWN PGK 06-04-1997				
E	CORRECTED IEC MARKINGS ECD-0111208	WGJ 01-23-2017	EMH	DEC.	INCHES			CHK	ML 06-05-1997			
D	RE-DRAWN WITH REGAL LOGO ECD-0110493	WGJ 09-30-2016	EMH	.X	±.1			APPD	GK 06-15-1997			
8	ADDED IEC DESIGNATIONS MU95020	TJW 4/30/2010	MJS	.XX	±.02	TITLE CONNECTION DIAGRAM DELTA CON. - 3Ø - 9 LEADS		SCALE				
7	REVISD HIGH VOLTAGE L2 WAS L3 CN52600-354	MRB 09-21-1998		.XXX	±.005			REF				
6	REDRAWN ON CADD	PGK 06-05-1997		.XXXX	±.0005	MAT'L.		FMF				
NO.	REVISION	BY & DATE	CHK	ANG	± 7'30"	FINISH		PREV				
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP		CAD FILE EE7308K			SIZE	DRAWING NO.	PAGE	OF	REV.
			DIST					A	EE7308K			E

CERTIFICATION DATA SHEET

Model#: 365TTFS16827 AN
 CONN. DIAGRAM: A-EE7308K
 OUTLINE: B-SS508590-1450

WINDING#: T367405 NONE 1
 ASSEMBLY: F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
75&60	56&45	1800	1780&1480	365T	TEFC	G	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	230/460#190/ 380	172/86&167/8 3.5	ACROSS THE LINE	CONTINUOU S	F3	1.15/1.15	40	3300

FULL LOAD EFF: 95.4&95	3/4 LOAD EFF: 95.4	1/2 LOAD EFF: 95	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 86&85	3/4 LOAD PF: 83.5	1/2 LOAD PF: 76	95	SQ CAGE IND RUN	56 / 28

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
221 LB-FT	1084 / 542	445 LB-FT 201	575 LB-FT 260	80

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
68 dBA	78 dBA	18.5 LB-FT^2	500 LB-FT^2	25 SEC.	2	1050 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	PREMIUM SEVERE DUTY	NONE	FALSE	NONE	BLUE (EPOXY)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL	BALL	POLYREX EM	T	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON
6314	6312						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further
information

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE
ENCODER: NONE
NONE NONE
NONE NONE PPR
BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

*
N
O
T
E
S
*

DATE: 06/22/2017 03:30:03 AM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.

Data Sheet

Date: 6/20/2017

Customer: _____

Attention: _____

Submitted by: FAREEDA DUDEKULA



365TTFS16827

Submittal

Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	28.0	34.0	49.0	66.5	86.0	98.5	108	542	
Torque (ft-lb)	0.00	55.0	110	166	221	255	278	445	
RPM	1800	1795	1790	1785	1780	1,775	1772	0	
Efficiency (%)		91.7	95.0	95.4	95.4	95.0	94.5		
P.F. (%)	4.5	56.0	76.0	83.5	86.0	86.5	86.5	35.5	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle																																									
Speed (RPM)	0	900	1725	1780	1800	Information Block																																								
Current (Amps)	542	500	300	86.0	28.0	HP	75.0																																							
Torque (ft-lb)	445	375	575	221	0.00	Sync. RPM	1800																																							
Efficiency (%) P.F. (%) Current (Amps) <table><thead><tr><th>LOAD</th><th>Efficiency (%)</th><th>P.F. (%)</th><th>Current (Amps)</th></tr></thead><tbody><tr><td>0%</td><td></td><td></td><td>46</td></tr><tr><td>20%</td><td>92</td><td>55</td><td>48</td></tr><tr><td>40%</td><td>94</td><td>75</td><td>55</td></tr><tr><td>60%</td><td>95</td><td>82</td><td>65</td></tr><tr><td>80%</td><td>95</td><td>85</td><td>75</td></tr><tr><td>100%</td><td>95</td><td>86</td><td>85</td></tr><tr><td>120%</td><td>94</td><td>87</td><td>100</td></tr><tr><td>125%</td><td></td><td></td><td>105</td></tr></tbody></table>						LOAD	Efficiency (%)	P.F. (%)	Current (Amps)	0%			46	20%	92	55	48	40%	94	75	55	60%	95	82	65	80%	95	85	75	100%	95	86	85	120%	94	87	100	125%			105	Frame	365			
						LOAD	Efficiency (%)	P.F. (%)	Current (Amps)																																					
						0%			46																																					
						20%	92	55	48																																					
						40%	94	75	55																																					
						60%	95	82	65																																					
						80%	95	85	75																																					
						100%	95	86	85																																					
						120%	94	87	100																																					
						125%			105																																					
						Enclosure	TEFC																																							
						Construction	TFS																																							
						Voltage	230/460#190/381V																																							
						Frequency	60	Hz																																						
						Design	A																																							
						LR Code letter	G																																							
						Service Factor	1.15																																							
Temp Rise @ FL	80	° C																																												
Duty	CONT																																													
Ambient	40	° C																																												
Elevation	1,000	feet																																												
Rotor/Shaft wk ²	18.5	Lb-Ft ²																																												
Ref Wdg	T367405	NONE																																												
Sound Pressure @ 1M	68	dBA																																												
VFD Rating	NONE																																													
Outline Dwg	B-SS508590-1450																																													
Conn. Diag	A-EE7308K																																													
Additional Specifications:																																														
0																																														
0																																														
EQUIV CKT (OHMS / PHASE)																																														
R1	R2	X1	X2	Xm																																										
0.0560	0.0360	0.3190	0.3860	9.2420																																										

Speed -Torque Curve

