

Nameplate Specifications

Output HP	75 Hp	Output KW	56.0 kW
Frequency	60 Hz	Voltage	230/460 V
Current	172.0/86.0 A	Speed	1775 rpm
Service Factor	1.15	Phase	3
Efficiency	94.1 %	Power Factor	85
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	365TDV	Enclosure	Explosion Proof Fan cooled
Thermal Protection	Thermostats (N/C)	Ambient Temperature	55 °C
Drive End Bearing Size	NU314	Opp Drive End Bearing Size	6312
UL	No	CSA	N
CE	N	IP Code	56
Hazardous Location	EXP PROOF CL I GR C&D T3C	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.079 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Roller
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7308AD	Outline Drawing	B-SS518555-1450

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/23/2022