

PRODUCT INFORMATION PACKET

Model No: 365TTGS18031
Catalog No: 365TTGS18031
75,1800,EPFC,365TSD,3/60/230/460

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E




Nameplate Specifications

Output HP	75 Hp	Output KW	56.0 kW
Frequency	60 Hz	Voltage	230/460 V
Current	180.0/90.0 A	Speed	1775 rpm
Service Factor	1.15	Phase	3
Efficiency	93 %	Power Factor	83.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	365TDV	Enclosure	Explosion Proof Fan cooled
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	NU314	Opp Drive End Bearing Size	6312
UL	No	CSA	N
CE	N	IP Code	54
Hazardous Location	EXP PROOF CL I GR D T2A	Number of Speeds	1


Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.084 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Roller
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS518555-1450	Connection Drawing	A-EE7308U

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/23/2022



A- EE7308U

				<div>✓</div> <div>MAX. SURFACE ROUGHNESS UNLESS NOTED OTHERWISE</div>	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL. ON XX± .02 XXX± .005 XXXX± .0005 ANGLES± 7°30"				
				MATL SPEC			DRAWN BY PGK	09-18-1996	
				FINISH	<div></div>		CHKD BY ML	10-02-1996	
8	10-02-1996	REDRAWN ON CADD & REVISE TO HAVE LEADS FOR HEATER MARK H1 OR H2 CN 22969	PGK	REFERENCE DRW.			WAUSAU, WISCONSIN 54401	APPD BY GK	10-02-1996
REV	DATE	CHANGE	NAME	PART NAME CONNECTION DIAGRAM DELTA CONN. - 3Ø - 1-2CKT/SPACE HEATER				DRWG NO A - EE7308U	
		SHOP BOOK	PURCHASED	DISTRIBUTION - WA - LB - WP - LM - BR			CADD FILE NO.	EE7308U	