

PRODUCT INFORMATION PACKET

Model No: 365TTGS11070
Catalog No: 365TTGS11070
75,1800,EPFC,365TDV,3/60/230/460

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E




Nameplate Specifications


Output HP	75 Hp	Output KW	56.0 kW
Frequency	60 Hz	Voltage	230/460 V
Current	176.0/88.0 A	Speed	1780 rpm
Service Factor	1.15	Phase	3
Efficiency	94.1 %	Power Factor	85
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	365TDV	Enclosure	Explosion Proof Fan cooled
Thermal Protection	Thermostats (N/C)	Ambient Temperature	50 °C
Drive End Bearing Size	NU314	Opp Drive End Bearing Size	6312
UL	No	CSA	N
CE	N	IP Code	56
Hazardous Location	EXP PROOF CL I GR D T3B	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.078 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Roller
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS518555-1450	Connection Drawing	A-EE7300AD

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/23/2022






CONNECT T1 TO LINE 1
 CONNECT T2 TO LINE 2
 CONNECT T3 TO LINE 3

4-5-6 CONNECTED TO
 CONTROL CIRCUIT

VIEW OF TERMINAL END

				TOLERANCES UNLESS SPECIFIED			DRAWN DRS 09-05-1996				
				DEC.	INCHES		CHK	ML	09-06-1996		
				.X	±.1		APPD	GK	09-06-1996		
				.XX	±.02		SCALE	1=1			
4	REDRAWN IN AUTOCAD	TAT 08-02-2004	ML	.XXX	±.005		TITLE CONNECTION DIAGRAM SINGLE VOLT – 3Ø MOTOR		REF		
3	REDRAWN ON CADD	DRS 09-06-1996		.XXXX	±.0005	MAT'L.		FMF			
NO.	REVISION	BY & DATE	CHK	ANG	± 7'30"	FINISH		PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE ee7300ad		SIZE	DRAWING NO.	PAGE	OF	REV.
			DIST				A	EE7300AD			