

Nameplate Specifications

Output HP	100 Hp	Output KW	75.0 kW
Frequency	60 Hz	Voltage	460 V
Current	115.0 A	Speed	1785 rpm
Service Factor	1	Phase	3
Efficiency	94.5 %	Power Factor	86.5
Duty	Continuous	Insulation Class	F
Design Code	INV	KVA Code	J
Frame	405TS	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermostat	Ambient Temperature	40 °C
Drive End Bearing Size	6313	Opp Drive End Bearing Size	6313
UL	Recognized	CSA	Y
CE	Y	IP Code	56
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.046 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	TS	Assembly/Box Mounting	F2/F1 CAPABLE
Inverter Load	CONSTANT 2:1		
Outline Drawing	SS509125-1675	Connection Drawing	EE7300S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/13/2022