

Nameplate Specifications

Output HP	60 Hp	Output KW	45.0 kW
Frequency	60 Hz	Voltage	460/796 V
Current	71.0/41.0 A	Speed	1115 rpm
Service Factor	1.15	Phase	3
Efficiency	87.5 %	Power Factor	90.5
Duty	Oil Well	Insulation Class	F
Design Code	D	KVA Code	G
Frame	405T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6316	Opp Drive End Bearing Size	6316
UL	No	CSA	N
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	.136 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Overall Length	34.31 in
Frame Length	17.00 in	Shaft Diameter	2.875 in
Shaft Extension	7.5 in	Assembly/Box Mounting	F2/F1 Capable
Connection Drawing	A-EE7304H	Outline Drawing	B-SS513937-1700