

# PRODUCT INFORMATION PACKET



Model No: 445TTFCD36526  
Catalog No: 445TTFCD36526  
150/125,1800/1500,TEFC,445TCV,3/60/50/460/380

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

**Technical Specifications**

Shaft Diameter	3.375 in		
Outline Drawing	TBD	Connection Drawing	EE7300QA

**This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/24/2023**


THREE PHASE – SINGLE VOLTAGE  
MOTOR – CONDUIT BOX @ 'A'

TO REVERSE ROTATION:  
INTERCHANGE ANY TWO LINE  
LEAD CONNECTIONS

NOTE FOR FACTORY USE ONLY:  
TO SURGE TEST:



FOR 3 LEAD COMMON CONNECT:  
CONNECT P1 TO T1 THEN P2 TO L1  
FOR 6 LEAD COMMON CONNECT:  
CONNECT P1 TO BOTH T1  
THEN P2 TO L1

IF MOTOR HAS MULTIPLE  
T'S PER LEAD CONNECT  
TOGETHER LIKE T'S



A-9806 DECAL

TERMINAL BLOCK WHEN SPECIFIED



VIEW OF TERMINAL END

				TOLERANCES UNLESS SPECIFIED		MARATHON ELECTRIC	DRAWNBISWA 25/09/2019		
				DEC.	INCHES		CHK	VY	25/09/2019
				.X	±	—	APPD		
				.XX	±	—	TITLE	CONNECTION DIAGRAM	SCALE 1=1
				.XXX	±	—		3Ø – SINGLE VOLT – MOTOR WITH PROTECTOR	REF EE7300QA
				.XXXX	±	—	MAT'L.		FMF
NO.	REVISION	BY & DATE	CHK	ANG	±	—	FINISH	PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT				RFP	CAD FILE EE7300QA		SIZE	DRAWING NO.	PAGE OF
				DIST	WA-LB-SB		A	EE7300QA	REV.